

[See all 24 Products in Family](#)

# Allied Vision Manta G-040 1/2.9" Color CMOS Camera

See More by [Allied Vision](#)



Allied Vision Manta GigE Cameras (Front)



Stock **#11-607** **1 In Stock**

[Similar Cameras](#)

1  **C\$980<sup>00</sup>**

**ADD TO CART**

### Volume Pricing

Qty 1+	<b>C\$980.00</b> each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

Color **Spectrum:**

### General

Color Camera **Type:**

Manta G-040C	<b>Model Number:</b>
Allied Vision	<b>Manufacturer:</b>
Manta	<b>Camera Series:</b>

## Physical & Mechanical Properties

71 x 44 x 29 (excludes connectors and lens mount)	<b>Dimensions (mm):</b>
190	<b>Weight (g):</b>
Full	<b>Housing:</b>

## Sensor

128MB	<b>Image Buffer:</b>
1/2.9"	<b>Sensor Format:</b>
0.40	<b>Resolution (Megapixels):</b>
286.00	<b>Frame Rate (fps):</b>
728 x 544	<b>Pixels (H x V):</b>
6.9 x 6.9	<b>Pixel Size, H x V (µm):</b>
4.96 x 3.72	<b>Sensing Area, H x V (mm):</b>
Sony IMX287	<b>Imaging Sensor:</b>
Progressive Scan CMOS	<b>Type of Sensor:</b>
Global	<b>Shutter Type:</b>
12 bit	<b>Pixel Depth:</b>
Via Software	<b>Exposure Time:</b>
74.3	<b>Dynamic Range (dB):</b>
GigE Vision v1.2, GenICam SFNC V1.2.1	<b>Machine Vision Standard:</b>

## Electrical

2.77 (12VDC External Power Supply)	<b>Power Consumption (W):</b>
------------------------------------	-------------------------------

## Hardware & Interface Connectivity

GigE	<b>Interface:</b>
GigE, RJ45 with Screw Locks	<b>Connector:</b>
Power Supply Required and Sold Separately. USA: <a href="#">#15-281</a> Europe: <a href="#">#15-281</a> Japan: <a href="#">#15-281</a> China: <a href="#">#15-281</a>	<b>Power Supply:</b>
2 opto-isolated inputs, 2 opto-isolated outputs	<b>GPIOs:</b>
Hardware Trigger (GPIO) or Software Trigger	<b>Synchronization:</b>
Back Panel	<b>Interface Port Orientation:</b>
12-pin Hirose (HR10)	<b>GPIO Connector Type:</b>

## Threading & Mounting

C-Mount	<b>Mount:</b>
1/4-20 with Tripod Mount Adapter <a href="#">#89-996</a>	<b>Mounting Threads:</b>

## Environmental & Durability Factors

+5 to +45 **Operating Temperature (°C):**

-10 to +70 **Storage Temperature (°C):**

---

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 240:**

---

## Product Details

- Ideal Analog Replacement
- Up to 1" Maximum Sensors
- Up to 125 fps
- 32MB of Onboard Memory

Allied Vision Manta GigE Cameras are an excellent choice for entry into using the GigE interface. Featuring an intuitive user interface as well as a powerful SDK, these cameras are an excellent value. With options from 0.3 MegaPixels to 12 MegaPixels, all sensors offered cover a wide array of applications. Allied Vision Manta GigE Cameras feature sensors from 1/4" to 1" in size. GigE Cable and Power Supply, both sold separately, are required for operation. Additional [GigE cables](#), [#89-996](#) 1/4-20 Mounting Plate, and [#62-712](#) 12 Pin I/O Cable are available.

## Calibration Services

---

;