

Allied Vision Manta G-917 1" Monochrome CCD Camera

See More by [Allied Vision](#)



Allied VSION Manta GigE Cameras (Front)



Stock **#88-463** [CONTACT US](#)

[Similar Cameras](#)

- 1 +

C\$4,013.80

ADD TO CART

Qty 1+

C\$4,013.80

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE

Type:
Monochrome Camera

Manufacturer: Allied Vision
Mounting Threads: ¼-20 with Tripod Mount Adapter #89-996
Image Buffer: 32MB
Camera Family: Manta
Model Number: Manta G-917B
Imaging Sensor: Sony ICX814
Type of Sensor: Progressive Scan CCD
Type of Shutter: Global
Camera Sensor Format: 1"
Resolution (MegaPixels): 9.10
Pixels (H x V): 3,384 x 2,710
Pixel Size, H x V (µm): 3.69 x 3.69
Sensing Area, H x V (mm): 12.5 x 10.0
Frame Rate (fps): 10.10
Pixel Depth: 8/14 bit
Exposure Time: Via Software
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power Supply Required and Sold Separately: USA: #15-281 Europe: #15-281 Japan: #15-281 China: #15-281
Power Consumption (W): 4 (12VDC External Power Supply)
GPIOs: 2 opto-isolated inputs, 2 opto-isolated outputs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 71 x 44 x 29 (excludes connectors and lens mount)
Weight (g): 150
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 60.0
Operating Temperature (°C): +5 to +45
Storage Temperature (°C): -10 to +70
GPIO Connector Type: 12-pin Hirose (HR10)
Machine Vision Standard: GigE Vision v1.2, GenICam SFNC V1.2.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

