

Allied Vision Prosilica GT1290 1/3" Color CCD Camera

See More by [Allied Vision](#)



Stock **#87-068** ☐ In Stock

[Similar Cameras](#)

1

C\$1,839.60

ADD TO CART

Qty 1+

C\$1,839.60

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Color Camera

Manufacturer:
Allied Vision

Mounting Threads:
1/4-20 with Tripod Mount Adapter [#87-412](#)

Image Buffer:

128MB
Camera Family: Prosilica GT
Model Number: GT 1290 C
Imaging Sensor: Sony ICX445
Type of Sensor: Progressive Scan CCD
Type of Shutter: Global
Camera Sensor Format: 1/3"
Resolution (MegaPixels): 1.20
Pixels (H x V): 1,280 x 960
Pixel Size, H x V (µm): 3.75 x 3.75
Sensing Area, H x V (mm): 4.8 x 3.6
Frame Rate (fps): 33.00
Pixel Depth: 8/14 bit
Exposure Time: 12µs - 60s
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power Supply Required and Sold Separately: USA: #15-281 Europe: #15-281 Japan: #15-281 China: #15-281
Power Consumption (W): 2.9 (12VDC External Power Supply) 3.5 (PoE)
GPIOs: 1 opto-isolated input, 2 opto-isolated outputs, 1 non-isolated input, 2 non-isolated outputs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 70.5 x 53.3 x 33 (excludes connectors and lens mount)
Weight (g): 211
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 58.3
Operating Temperature (°C): -20 to +65
Storage Temperature (°C): -20 to +70
GPIO Connector Type: 12-pin Hirose (HR10)
Machine Vision Standard: GigE Vision V1.2, GenICam SFNC V1.2.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant