



Hoya B410 (UV-VIS) 25.4mm Dia.,. Colored Glass Bandpass Filter

See More by [Hoya](#)



Stock **#34-433** ☐ In Stock

1

C\$88.20

ADD TO CART

Qty 1-10
C\$88.20
Qty 11+
C\$78.40
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40

Center Wavelength CWL (nm):
410.00

Density (g/cm³): 2.27
Full Width-Half Max FWHM (nm): 232.00
Glass/Filter Number: Hoya B410
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Blue
Surface Quality: 80-50
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.2
Type: Bandpass Filter
Wavelength: UV-Vis
Parallelism (arcmin): ≤1
Dimensional Tolerance (mm): +0/-0.25

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View