

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#) / [Basler ace2 GigE/5GigE Cameras](#)

[See all 53 Products in Family](#)

Basler ace2 a2A2590-22gcPRO Color GigE Pro Camera



Basler ace2 GigE Cameras (Front)



Stock **#16-608** [CONTACT US](#)

[Similar Cameras](#)

[-](#) 1 [+](#)

C\$586.60

ADD TO CART

Qty 1+

C\$586.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Color Camera

Manufacturer:
Basler

Mounting Threads:

1/4-20 with Tripod Mount Adapter [#16-641](#)

Image Buffer: Not Specified
Camera Family: ace2
Model Number: a2A2590-22gcPRO
Imaging Sensor: Sony IMX334
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Rolling
Camera Sensor Format: 1/2.8"
Resolution (MegaPixels): 5.00
Pixels (H x V): 2,592 x 1,944
Pixel Size, H x V (µm): 2.00 x 2.00
Sensing Area, H x V (mm): 5.2 x 3.9
Frame Rate (fps): 22.00
Pixel Depth: 8/10/12 bit
Exposure Time: Freely Programmable
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power over Ethernet (PoE) or via GPIO with #16-644
Power Consumption (W): 3.3
GPIOs: 1 opto-coupled input line, 2 general purpose I/O (GPIO) lines
Synchronization: Hardware Trigger (GPIO), Software Trigger, or Free-Run
Dimensions (mm): 55.5 x 29 x 29 (excludes connectors and lens mount)
Weight (g): <105
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 69.5
Operating Temperature (°C): -10 to +60
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin M8
Machine Vision Standard: GigE Vision 2.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant