

SCHOTT BG25, 25.4mm Dia., 3mm Thick, Colored Glass Bandpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#84-901** ☐ In Stock

1

C\$65.80

ADD TO CART

Qty 1-10
C\$65.80
Qty 11+
C\$57.40
Volume Pricing
Request Quote

Get Product Downloads
Diameter (mm): 25.40
Center Wavelength CWL (nm): 400.00
Density (g/cm³):

2.56
Glass/Filter Number: SCHOTT BG25
Coating: Uncoated
Color: Blue-Violet
Surface Quality: 80-50
Thickness (mm): 3.00 ±0.2
Type: Bandpass Filter
Wavelength: UV-VIS
Note: Intense UV radiation can cause a reduction in transmission
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View