

TECHSPEC® C-Mount Achromat Pair 1:3.33 with 30 and 100mm Focal Lengths



Stock **#87-187** ☐ In Stock

-

1

+

C\$518.00

ADD TO CART

Qty 1-5
C\$518.00
Qty 6+
C\$414.40
Volume Pricing
Request Quote

Get Product Downloads

Surface Quality:
40-20

Working f#:
f/4.3 - f/125

Coating:
VIS 0° (425-675nm)

Coating Specification:
R_{avg} ≤0.4% @ 425 - 675nm

Aperture (mm): 0.8 - 20
Effective Focal Length EFL A (mm): 30.0
Effective Focal Length EFL B (mm): 100.0
Housing Diameter (mm): 38.00
Housing Length (mm): 45.9
Magnification: 1:3.33
Object Distance (mm): 15.00
Image Distance (mm): 75.00
Type: Relay Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 211: Compliant
Certificate of Conformance: View