

TECHSPEC[®] C-Mount, Fiber Connector Adapter Housing



C-Mount Connector Insert Housing, #66-385

Stock **#66-385** 20+ In Stock

-

1

+

C\$53⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$53.66 each
Qty 5-9	C\$47.78 each
Qty 10-25	C\$44.54 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Function:

Optic Mount (Fixed)

Physical & Mechanical Properties

9.20	Thickness (mm):
Black Anodized Aluminum	Construction:
30.0	Outer Diameter (mm):
Threading & Mounting	
C-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

PRODUCT DETAILS

- C-Mount, S-Mount, SM1, and SM05 Threading
- Low Profile Designs for Mniml System Intrusion
- Available for SMA, FC, or FC/APC Fiber Connectors

Tube System Fiber Connector Adapters provide an easy and simple solution for integrating connectorized fiber into C-Mount, S-Mount, SM1 (1.035" x 40 TPI), or SM05 (0.535" x 40 TPI) systems. C-Mount Fiber Connector Adapters are available for SMA, FC, or FC/APC connectors. S-Mount Fiber Connector Adapters are available for SMA, FC, or FC/APC connectors. SM1 and SM05 Fiber Connector Adapters are available for FC/APC connectors. Connectors can be threaded into any female [C-Mount](#), [S-Mount](#), [SM1](#), or [SM05](#) component. Tube System Fiber Connector Adapters can be oriented in either direction for maximum flexibility. Optional housings are sold separately.

TECHNICAL INFORMATION

