

C-mount Electrical Shutter



C-mount Electrical Shutter, #87-208

Stock **#87-208** ☐ In Stock



1



C\$680.40

ADD TO CART

Qty 1-4

C\$680.40

Qty 5+

C\$600.32

Volume Pricing

[Request Quote](#)

Get Product Downloads

Outer Diameter (mm):
60.0

Activation Time (ms):
30

Aperture (mm):
20.0

Coil Resistance (Ω):

90 @ 25°C
Coil Resistance Tolerance (%) : ±10
Deactivation time (ms) : 50
Mount : C-Mount
Operating Temperature (°C) : -20 to +70
Operating Voltage (V) : 4.5 V~ 5.5 VDC
Output Current (mA) : 32.00
Weight (g) : 80
Function : Shutter
Thread Type : C-Mount
Operating Frequency (Hz) : 12.5 for Full Open/Closed 30 for Non-Full Open/Close
Operating Life Cycle : 300,000
Compatible Post : M6 x 1.0, 1/4-20
Extension Length (mm) : 13.0

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View