

TECHSPEC® C-Mount Extension Tube Kit



Stock **#54-668** **4 In Stock**

- 1 + C\$513⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-4 | C\$513.80 each |
| Qty 5-9 | C\$453.18 each |
| Qty 10-25 | C\$417.34 each |
| Need More? | Request Quote |

Product Downloads

General

C-Mount Kit **Type:**

Extension Tube (Fixed) **Function:**

Contents of Kit:
5mm: [#54-628](#), 10mm: [#54-629](#), 15mm: [#54-630](#),
50mm: [#54-632](#), 100mm: [#54-633](#)

Physical & Mechanical Properties

22.0 Clear Aperture CA (mm):

30.0 Outer Diameter (mm):

Threading & Mounting

C-Mount Thread Type:

Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 235:

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

Technical Information

