

TECHSPEC[®] C-Mount Male Aperture Cap



C-Mbunt Male Aperture Cap

Stock #58-199 3 In Stock

-

1

+

C\$24¹⁵

ADD TO CART

Volume Pricing	
Qty 1-9	C\$24.15 each
Qty 10+	C\$21.56 each
Need More?	Request Quote

Product Downloads

General

Tube Cap

Function:

Physical & Mechanical Properties

31.70

Diameter (mm):

3.0

Total Length (mm):

Thickness (mm):

Threading & Mounting

C-Mount

Thread Type:

Regulatory Compliance

Compliant

RoHS 2015:

View

Certificate of Conformance:

Product Details

- C, S, and T-Mount Solutions for Mounting Cube and Plate Beamsplitters, Filters, and Mirrors
 - Provides a 90° Mounting Interface
 - ¼-20 and M6 Tapped Mounting Threads for English or Metric Based Systems
- TECHSPEC® C, S, and T-Mount Cube and Plate Mounts allow for the integration of cube and plate optics into C, S, and T-Mount systems. These mounts feature four C, S, or T-Mount threaded apertures that can also act as connection points for other C, S, or T-Mount components. Either an M6 or 1/4-20 tapped hole is provided on the base for post mounting, making these mounts compatible with breadboard and benchtop systems. TECHSPEC C, S, and T-Mount Cube and Plate Mounts provide a 90° mounting interface ideal for placing beamsplitters, filters, and mirrors within a system. C, S, and T-Mount Aperture Caps are available to block light from unused openings and to protect the optic from dust and debris.

Note: [#11-139](#) and [#11-142](#) each include one S-Mount Aperture Cap ([#11-137](#))

Technical Information

