

**TECHSPEC** Cage Plate Angle Bracket



#85-664

Stock **#85-664** **2 In Stock**

⊖ 1 ⊕ C\$21<sup>70</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	C\$21.70 each
Need More?	<a href="#">Request Quote</a>

Product Downloads

**General**

Angle Adjustment **Function:**

**Physical & Mechanical Properties**

Black Anodized Aluminum **Construction:**

9.5x15.2 **Dimensions (mm):**

**Regulatory Compliance**

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

---

[Compliant](#) **REACH 241:**

---

## Product Details

- Multiple Angular Positioning Options
- Fixed and Continuous Adjustment Plates Available
- Anodized Aluminum Construction

TECHSPEC® Cage System Angle Adjustment Plates attach to [standard mounting plates](#) via angle brackets, and offer a range of angular positioning options. The fixed angle mounting plates feature M3 C-Bore holes positioned at 30° increments to introduce 30°, 60°, or 90° bends in the optical path. Swivel adapter plates are designed to be used in pairs, and enable continuous angle adjustment. [#85-692](#) or [#85-701](#) post adapter for 25mm plates serves as a joint between two swivel adapter plates. Suspending a tilt plate between two standard cage system plates allows an optic or mount to be tilted with respect to the optical axis.

### Quick Video Demonstration

Maximize your application performance with the right products. View a quick video demonstration of TECHSPEC Cage System components: [How to Build a Swivel Joint Assembly](#).

---

;