

Cat 6a M12 to RJ45 Ethernet Dragchain Cable, IP65/67, 10m

See More by [IDS Imaging Development Systems](#)



Stock **#19-699** **7 In Stock**

-

1

+

C\$267⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$267.40 each
Need More?	Request Quote

Product Downloads

General

Camera Accessory

Type:

Dragchain, M12 to RJ45 Connector

Note:

Hardware & Interface Connectivity

10

Length of Cable (m):

Cat 6a, M12

Connector:

Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Designed for Harsh Environments
- Robust IP65/67 Housing for Dust and Washdown Protection
- Compatible with [TECHSPEC® Cw Series Lenses](#)
- IP65/67 Rated Accessories and Illumination Also Available

IDS Imaging uEye+ FA IP65/67 PoE Cameras feature robust IP65/67 rated housings to withstand harsh industrial environments, providing protection against dirt, dust, and water. These cameras provide plug-and-play functionality and require no additional enclosures when paired with [TECHSPEC® Cw Series Lenses](#). Featuring IP65/67 rated accessories, these cameras utilize IDS Imaging's latest Peak SDK platform that supports GenICam and GigE Vision standards, simplifying system integration and software development. IDS Imaging uEye+ FA IP65/67 PoE Cameras are ideal for a wide variety of demanding applications requiring washdown and dust resistance including factory automation, medical technology, and machine vision.