

Coarse Movement, 50mm Diameter Thru Hole, Rack & Pinion



50mm Diameter Thru Hole

Stock **#03-609** **20+ In Stock**

⊖ 1 ⊕ C\$560⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$560.00 each
Need More?	Request Quote

Product Downloads

General

Rack and Pinion Mount **Type:**

50 mm Diameter Thru-Hole **Note:**

Coarse Movement **Type of Adjustment:**

Physical & Mechanical Properties

Dimensions (mm):
Rack and Pinion Block: 50.8 H x 28.6 W x 50.8 L

35 (+23/-12) in Y	Travel (mm):
1.31	Weight (lbs):
25.5	Travel Per Knob Rotation (mm):
2.00	Load Capacity (kg):
Linear (Y)	Type of Movement:
100.00	Optical Centerline from Post (mm):

Threading & Mounting

Mounting Post Hole and Thread:
3/4" Diameter Post 1/4-20 Tapped Hole

Regulatory Compliance

RoHS 2015:	Exempt
Reach 224:	Contains SVHC(s)
Certificate of Conformance:	View

Product Details

- Coarse or Fine Motion Available
- Thru Holes for Integrating Lenses
- 1/4-20 Stud for Mounting Cameras
- [Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) also Available

Rack and Pinion Focusing Mounts for Imaging Systems add additional focus ability to imaging systems. Thru Holes are ideal for use with [TECHSPEC® VZM™ Zoom Imaging Lenses](#) or other imaging lenses. Rack and Pinion Movement with 1/4-20 stud can be used with any compatible camera or imaging lens. Rack and Pinion Focusing Mounts for Imaging Systems are offered with either coarse or fine motion. [Imaging System Bases](#), [Stainless Steel Posts](#), and [Accessories](#) are also available.

;