

Coherent® OBIS™ 1233470 | 594nm LS 60mW Laser

See More by [Coherent®](#)



Stock **#12-356** [CONTACT US](#)

- 1 +

C\$12,376.00

ADD TO CART

Qty 1+

C\$12,376.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
15 to 40

Output Power (mW):
60

Polarization:
100:1

Power Stability (%): <2
Spatial Mode: TEM ₀₀
Wavelength (nm): 594.00 ±2
Mode Quality, M²: ≤1.1
Power Supply: Power Supply Required and Sold Separately. USA: #87-473 Europe: #87-473 Japan: #87-473 Korea: #87-473 China: #87-473
Warm-Up Time (minutes): <5
Pointing Stability (μrad/°C): <5
Modulation Frequency (MHz): Max Digital: 0.05
Modulation Frequency (kHz): Max Analog: 100
Beam Diameter Tolerance (mm): ±0.05
Pointing Stability (μrad): <30
RMS Noise: ≤0.25% (20Hz to 20MHz)
Beam Diameter (mm): 0.7
Manufacturer: Coherent®
Output Type: Free Space
Type of Laser: Diode
Beam Divergence (mrad): Full-Angle: ≤1.3
Laser Class - CDRH: IIIb
Color: Orange
Model Number: 1233470

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View