

Coherent® OBIS™ 1280718 | 532nm LS 150mW Laser

See More by [Coherent®](#)



Stock **#12-348** [CONTACT US](#)

-

1

+

C\$14,350.00

ADD TO CART

Qty 1+

C\$14,350.00

Volume Pricing

[Request Quote](#)

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):  
15 to 40

Output Power (mW):  
150

Polarization:  
100:1

|                                                                                                                                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Power Stability (%):</b><br><2                                                                                                                                                                                                           |
| <b>Spatial Mode:</b><br>TEM <sub>00</sub>                                                                                                                                                                                                   |
| <b>Wavelength (nm):</b><br>532.00 ±2                                                                                                                                                                                                        |
| <b>Mode Quality, M<sup>2</sup>:</b><br>≤1.1                                                                                                                                                                                                 |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#87-473</a><br>Europe: <a href="#">#87-473</a><br>Japan: <a href="#">#87-473</a><br>Korea: <a href="#">#87-473</a><br>China: <a href="#">#87-473</a> |
| <b>Warm-Up Time (minutes):</b><br><5                                                                                                                                                                                                        |
| <b>Pointing Stability (μrad/°C):</b><br><5                                                                                                                                                                                                  |
| <b>Modulation Frequency (MHz):</b><br>Max Digital: 0.05                                                                                                                                                                                     |
| <b>Modulation Frequency (kHz):</b><br>Max Analog: 100                                                                                                                                                                                       |
| <b>Beam Diameter Tolerance (mm):</b><br>±0.05                                                                                                                                                                                               |
| <b>Pointing Stability (μrad):</b><br><30                                                                                                                                                                                                    |
| <b>RMS Noise:</b><br>≤0.25% (20Hz to 20MHz)                                                                                                                                                                                                 |
| <b>Beam Diameter (mm):</b><br>0.7                                                                                                                                                                                                           |
| <b>Manufacturer:</b><br>Coherent®                                                                                                                                                                                                           |
| <b>Output Type:</b><br>Free Space                                                                                                                                                                                                           |
| <b>Type of Laser:</b><br>Diode                                                                                                                                                                                                              |
| <b>Beam Divergence (mrad):</b><br>Full-Angle: ≤1.2                                                                                                                                                                                          |
| <b>Laser Class - CDRH:</b><br>IIIb                                                                                                                                                                                                          |
| <b>Color:</b><br>Green                                                                                                                                                                                                                      |
| <b>Model Number:</b><br>1280718                                                                                                                                                                                                             |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |