

Preloaded Norland Optical Adhesive NOA 146H Dispensing Barrel (3cc)

See More by [Norland](#)



3cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#12-864** ☐ In Stock

-

1

+

C\$37.10

ADD TO CART

Qty 1-4
C\$37.10
Qty 5+
C\$35.56
Volume Pricing
Request Quote

Get Product Downloads
Size (oz): 0.1
Glass Bonding: Excellent
Metal Bonding: Good

Plastic Bonding: Fair
Viscosity (cps): 175
Durability: Hard
Index of Refraction n_d: 1.46 @ 589nm
Norland Number: 146H
Shelf Life: 4 months
Type: Barrel
Typical Applications: Low viscosity adhesive for bonding glass or plastic. Cured with UV light and/or heat.
Note: Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.
Absorption Range (nm): 320 - 395
Bonding Type: Plastic to Plastic/Glass
Energy for Full Cure (J/cm²): 4.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant