

# Preloaded Norland Optical Adhesive NOA 65 Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA (NOA60 shown as an example)

Stock **#55-087** ☐ In Stock

-

1

+

C\$45.50

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-4                       |
| C\$45.50                      |
| Qty 5+                        |
| C\$43.96                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

|                        |
|------------------------|
| Get Product Downloads  |
| Size (oz):<br>0.34     |
| Size (cc):<br>10.00    |
| Glass Bonding:<br>Good |

|                                                                                                                                    |
|------------------------------------------------------------------------------------------------------------------------------------|
| <b>Metal Bonding:</b><br>Good                                                                                                      |
| <b>Plastic Bonding:</b><br>Fair                                                                                                    |
| <b>Viscosity (cps):</b><br>1200                                                                                                    |
| <b>Durability:</b><br>Flexible                                                                                                     |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.52 @ 589nm                                                                       |
| <b>Norland Number:</b><br>65                                                                                                       |
| <b>Shelf Life:</b><br>6 months                                                                                                     |
| <b>Type:</b><br>Barrel                                                                                                             |
| <b>Typical Applications:</b><br>More flexible adhesive for extra low strain applications. Suitable for cold blocking applications. |
| <b>Note:</b><br>Contains 10g of adhesive                                                                                           |
| <b>Absorption Range (nm):</b><br>350 - 380                                                                                         |
| <b>Bonding Type:</b><br>Glass to Glass/Metal                                                                                       |
| <b>Energy for Full Cure (J/cm<sup>2</sup>):</b><br>4.5                                                                             |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Compliant</a>             |

---