

Preloaded Norland Optical Adhesive NOA 86H Dispensing Barrel (10cc)

See More by [Norland](#)



10cc Dispensing Barrel for NOA

Stock **#12-847** [CONTACT US](#)

- 1 + **C\$45.50**

ADD TO CART

Qty 1-4
C\$45.50
Qty 5+
C\$43.96
Volume Pricing
Request Quote

Get Product Downloads
Size (oz): 0.34
Glass Bonding: Excellent
Metal Bonding: Good

Plastic Bonding: Excellent/Good
Viscosity (cps): 250 - 350
Durability: Hard
Index of Refraction n_d: 1.55 @ 589nm
Norland Number: 86H
Shelf Life: 4 months
Type: Barrel
Typical Applications: Meets Bellcore specification of 85C/85RH for bonding glass. USP Class IV approved for medical applications. Cured with UV, visible light and/or heat.
Note: Contains 10g of adhesive. This adhesive should be refrigerated between 5 - 10°C when stored to maintain its optical properties.
Absorption Range (nm): 315 - 420
Bonding Type: Glass to Glass/Plastic
Energy for Full Cure (J/cm²): 2.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant