

Polarizing Film for 300 x 300 Active Area



Stock **#22-112** [CONTACT US](#)

-

1

+

C\$924^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$924.00 each
Need More?	Request Quote

Product Downloads

General

Model Number:	EFFO-FD-POL-300-300-KIT
Manufacturer:	Effilux

Hardware & Interface Connectivity

Power Supply:	Power Supply Required and Sold Separately.
	USA: #15-874
	Europe: #15-875
	Japan: #73-409
	Korea: #73-409
	China: #15-874

Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Dome Light Performance in a Flat Housing
- Integrated Analog Controller for Precise Intensity and Dimming
- Anti-Reflection System to Absorb Stray Light
- Continuous or Strobe mode

Effilux Flat Dome Lights achieve diffuse illumination similar to standard dome lights but with a thinner, more compact housing. These flat dome lights provide a large imaging area for increased depth of focus and field of view. The convenient integrated analog controller allows precise control of power and intensity without the need for additional components. Effilux Flat Dome Lights offer greater than 90% uniformity and feature an anti-reflection system that absorbs unwanted light. Flat Dome Lights are ideal for imaging textured, shiny, or uneven surfaces.