

EO-3AN 1/3" CCD Color Analog Camera, NTSC



Stock **#88-408** [CONTACT US](#)

-

1

+

C\$693.00

ADD TO CART

Qty 1+

C\$693.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Video Output:
Analog

Type:
Color Camera

Mounting Threads:
1/4-20 (Integrated into Housing)

Image Buffer:
Not Specified

Model Number: EO-3AN
Type of Sensor: Interlaced CCD
Camera Sensor Format: 1/3"
Resolution (MegaPixels): 0.40
Pixels (H x V): 976 x 494
Pixel Size, H x V (µm): 4.9 x 6.9
Sensing Area, H x V (mm): 4.8 x 3.4
Exposure Time: Auto/Manual 1/60-1/100,000s
Connector: Analog, BNC, Y-C
Power Supply: Separate Power Supply (Included)
Power Consumption (W): 2.5
GPIOs: N/A
Synchronization: Internal
Dimensions (mm): 51.6 x 41 x 41 (includes connectors and lens mount)
Weight (g): 140
Mount: C/CS-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): Not Specified
Operating Temperature (°C): -10 to +50
GPIO Connector Type: None
Power Requirement: 12 VDC
Signal Format: NTSC

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View