

## EO-3BW 1/3" CCD Analog Monochrome Camera



Stock #58-253 **7 In Stock**

- 1 + C\$686.00

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$686.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

Monochrome **Spectrum:**

### General

Monochrome Camera **Type:**

EO-3BW **Model Number:**

### Physical & Mechanical Properties

**Dimensions (mm):**  
56 x 41 x 41 (includes connectors and lens mount)

**Weight (g):**  
140

**Housing:**  
Full

## Sensor

**Image Buffer:**  
Not Specified

**Sensor Format:**  
1/3"

**Resolution (Megapixels):**  
0.30

**Pixels (H x V):**  
768 x 494

**Pixel Size, H x V (µm):**  
6.4 x 7.4

**Sensing Area, H x V (mm):**  
4.8 x 3.6

**Type of Sensor:**  
Interlaced CCD

**Exposure Time:**  
1/60 - 1/100,000s, On/Off

**Dynamic Range (dB):**  
Not Specified

**Signal Format:**  
EIA(RS-170)

## Electrical

**Power Consumption (W):**  
1.2

## Hardware & Interface Connectivity

**Interface:**  
Analog

**Connector:**  
Analog, BNC

**Power Supply:**  
Separate Power Supply (Included)

**GPIOs:**  
N/A

**Synchronization:**  
Internal

**Interface Port Orientation:**  
Back Panel

**GPIO Connector Type:**  
None

**Power Requirement:**  
12 VDC

## Threading & Mounting

**Mount:**  
C/CS-Mount

**Mounting Threads:**  
1/4-20 (Integrated into Housing)

## Environmental & Durability Factors

**Operating Temperature (°C):**  
-10 to +50

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- 1/2" or 1/3" Format CCD Available
- Improved Resolution
- C-Mount Adapter Included
- Power Supply Included

