

EO-3BW 1/3" CCD Analog Monochrome Camera



Stock #58-253 7 In Stock

-

1

+

C\$686⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$686.00 each
Need More?	Request Quote

Product Downloads

Spectrum:	
Monochrome	
General	
Type:	
Monochrome Camera	
Model Number:	
EO-3BW	

Physical & Mechanical Properties

56 x 41 x 41 (includes connectors and lens mount)	Dimensions (mm):
140	Weight (g):
Full	Housing:
Sensor	
Not Specified	Image Buffer:
1/3"	Sensor Format:
0.30	Resolution (Megapixels):
768 x 494	Pixels (H x V):
6.4 x 7.4	Pixel Size, H x V (µm):
4.8 x 3.6	Sensing Area, H x V (mm):
Interlaced CCD	Type of Sensor:
1/60 - 1/100,000s, On/Off	Exposure Time:
Not Specified	Dynamic Range (dB):
EIA(RS-170)	Signal Format:
Electrical	
1.2	Power Consumption (W):
Hardware & Interface Connectivity	
Analog	Interface:
Analog, BNC	Connector:
Separate Power Supply (Included)	Power Supply:
N/A	GPIOs:
Internal	Synchronization:
Back Panel	Interface Port Orientation:
None	GPIO Connector Type:
12 VDC	Power Requirement:
Threading & Mounting	
C/CS-Mount	Mount:
1/4-20 (Integrated into Housing)	Mounting Threads:
Environmental & Durability Factors	
-10 to +50	Operating Temperature (°C):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- 1/2" or 1/3" Format CCD Available
- Improved Resolution
- C-Mount Adapter Included
- Power Supply Included

