

Astronomy Bandpass Filter, Kron-Cousins, UV 50 x 50mm



Astronomy Bandpass Filters

Stock **#21-115** ☐ In Stock

-

1

+

C\$1,124.20

ADD TO CART

Qty 1-5
C\$1,124.20
Qty 6+
C\$1,011.78
Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm): 50 x 50
Center Wavelength CWL (nm): 365.00
Full Width-Half Max FWHM (nm): 60.00
Type of Filter:

Kron-Cousins, U
Minimum Transmission (%): >50
Surface Quality: 60-40
Thickness (mm): 5.00 ±0.1
Type: Bandpass Filter
Dimensional Tolerance (mm): +0/-0.25
Transmitted Wavefront, RMS: λ/4
Parallelism (arcsec): <30

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant