

Flip Mount, Metric



Flip Mount



Stock **#19-408** **8 In Stock**

-

1

+

C\$138⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-24	C\$138.60 each
Qty 25-49	C\$108.50 each
Need More?	Request Quote

Product Downloads

General	
Flip Mount	Function:
Metric	Type:
Physical & Mechanical Properties	
	Thickness (mm):

25.40	
Black Anodized Aluminum	Construction:
<100	Repeatability (μrad):
Threading & Mounting	
M4 Cbore, M6 x 1.0 Female, M4 x 0.7 Female	Mounting Threads:
M6 x 1.0, M4 x 0.7	Compatible Post:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- 25.4mm Mount Thickness Maintains Simple and Consistent Mounting Heights
- <100μrad Angular Repeatability
- Available with English or Metric Mounting Threads

90° Flip Mounts are ideal for easily flipping mounted optics in and out of a beam path. An angular repeatability of <100μrad helps to ensure mounted optics maintain alignment relative to the optical path after repeated adjustments of the mount. These flip mounts feature both female threaded and counterbored mounting holes for added versatility. 90° Flip Mounts are designed with a 25.4mm (1") thickness to maintain simple and consistent operating heights between optical elements when mounted to an [optical post](#). The mounting holes are available in both Metric (M4 tap and M4 counterbore with internal M6 threading), or English (8/32 tap and 8/32 counterbore with internal 1/4-20 threading) options for adaptability in any benchtop optical system.