

G Plan Apo 20X Objective

See More by [Mitutoyo](#)



Stock #58-175 ☐ In Stock

-

1

+

C\$6,251.00

ADD TO CART

Qty 1+
C\$6,251.00

Volume Pricing
Request Quote

Get Product Downloads

Compatible Cover Glass Thickness (mm): 3.5
Horizontal Field of View, 1/2" Sensor: 0.32mm
Horizontal Field of View, 2/3" Sensor: 0.44mm
Focal Length FL (mm): 10.00
Model Number: 378-847

Length excluding Threads (mm): 65.60
Magnification: 20X
Maximum Diameter (mm): 34
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.28
Mounting Threads: M26 x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 1.0
Depth of Field (µm): 3.50
Field of View, 24 Diameter Field Eyepiece (mm): 1.20
Operating Temperature (°C): +5 to +40
Operating Humidity: 20 - 80%
Working Distance (mm): 29.42 (30.60 through compatible cover glass)
Weight (g): 270.00
Wavelength Range (nm): 436 - 656
Style: Infinity Corrected
Manufacturer: Mitutoyo
Parfocal Length (mm): 96.19
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)