

SCHOTT GG-495, 25.4mm Dia., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#32-753** ☐ In Stock

1

C\$54.25

ADD TO CART

Qty 1-10
C\$54.25
Qty 11+
C\$53.20
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):

25.40

Cut-Off Position λ_c (nm):

495±6

Cut-On Wavelength (nm):

495.00
Density (g/cm³): 2.56
Glass/Filter Number: SCHOTT GG495
Coating: Uncoated
Color: Yellow
Passband Limit 1 λ_{p1} (nm): 560.00
Spectral Transmittance t_p (%): 92.00
Stopband Limit λ_s (nm): 430.00
Surface Quality: 80-50
Transformation Temperature (°C): 535.00
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.38
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Compliant
Certificate of Conformance: View