

Green M62 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-624 ☒ In Stock



1



C\$376.60

ADD TO CART

Qty 1-9

C\$376.60

Qty 10+

C\$357.84

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):

200-470, 600-963

Clear Aperture CA (mm):

57.10

Coating:

Hard Coated

Filter Thread:

M62 x 0.75
Color: Green
Center Wavelength CWL (nm): 525.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 80.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 64.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View