

Green M72 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock **#21-590** ☐ In Stock



1



C\$484.40

ADD TO CART

Qty 1-9

C\$484.40

Qty 10+

C\$460.32

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):

200-470, 600-961

Clear Aperture CA (mm):

67.50

Coating:

Hard Coated

Filter Thread:

M72 x 0.75
Color: Green
Center Wavelength CWL (nm): 525.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 80.00
Mount Thickness (mm): 6.0
Mount Thickness Including Threads (mm): 8.3
Outer Diameter (mm): 75.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View