

GS3-U3-23S6C-C 1/1.2" FLIR Grasshopper®3 High Performance USB 3.0 Color Camera

See More by [FLIR](#)



FLIR Grasshopper®3 High Performance USB 3.0 Cameras (Front)



Stock **#88-608** ☐ In Stock

[Similar Cameras](#)

1

C\$1,650.60

ADD TO CART

Qty 1+
C\$1,650.60
Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
USB 3.0

Type:
Color Camera

Manufacturer: FLIR
Mounting Threads: ¼-20 with Tripod Mount Adapter #88-057
Image Buffer: 128MB
Camera Family: Grasshopper®3
Model Number: GS3-U3-23S6C-C
Imaging Sensor: Sony IMX174
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/1.2"
Resolution (MegaPixels): 2.30
Pixels (H x V): 1,920 x 1,200
Pixel Size, H x V (µm): 5.86 x 5.86
Sensing Area, H x V (mm): 11.25 x 7.03
Frame Rate (fps): 162.00
Pixel Depth: 8/12/16/24 bit
Exposure Time: 5µs - 31.9s
Connector: USB 3.1 Gen 1, Micro-B with Screw Locks
Power Supply: Power over USB (required for operation) #86-770 or via GPIO with #86-784
Power Consumption (W): 4.5
GPIOs: 1 opto-isolated input, 2 opto-isolated outputs, 2 non- isolated bi-directional ports
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 44 x 29 x 57.5 (excludes connectors and lens mount)
Weight (g): 90
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 67.37
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -30 to +60
GPIO Connector Type: 8-pin Hirose (HR25)
Machine Vision Standard: USB3 Vision v1.0
Transfer Speed (Gbit/s): 5.00

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance:

