

## Hi-Res 6.0mm Lens, PAL, Color DSP Board Level Camera



Stock #57-251 CLEARANCE ☐ In Stock

- 1 + **C\$139.93**

ADD TO CART

|           |
|-----------|
| Qty 1+    |
| C\$139.93 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

|                       |
|-----------------------|
| Get Product Downloads |
|-----------------------|

|                                                                |
|----------------------------------------------------------------|
| <b>Video Output:</b><br>Analog                                 |
| <b>Type:</b><br>Color Camera                                   |
| <b>Mounting Threads:</b><br>No Mounting Threads/Tripod Adapter |
| <b>Working Distance (mm):</b><br>250 - ∞                       |
| <b>Image Buffer:</b><br>Not Specified                          |

|                                                                       |
|-----------------------------------------------------------------------|
| <b>Type of Sensor:</b><br>Interlaced CCD                              |
| <b>Camera Sensor Format:</b><br>1/4"                                  |
| <b>Resolution (MegaPixels):</b><br>0.40                               |
| <b>Pixels (H x V):</b><br>752 x 582                                   |
| <b>Exposure Time:</b><br>1/60 - 1/100,000s                            |
| <b>Connector:</b><br>Analog, 10" Wire Leads                           |
| <b>Power Supply:</b><br>Separate Power Supply <a href="#">#62-941</a> |
| <b>GPIOs:</b><br>N/A                                                  |
| <b>Dimensions (mm):</b><br>20 x 32 x 32 (excludes lens mount)         |
| <b>Weight (g):</b><br>30                                              |
| <b>Mount:</b><br>Lens Included                                        |
| <b>Housing:</b><br>Board Level                                        |
| <b>Interface Port Orientation:</b><br>Front/Back Panel                |
| <b>Operating Temperature (°C):</b><br>-10 to +50                      |
| <b>Storage Temperature (°C):</b><br>-20 to +60                        |
| <b>Power Requirement:</b><br>12 VDC, 130 mA                           |
| <b>Signal Format:</b><br>PAL, Y-C                                     |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |