

Hoya L38 (380nm), 12.5mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock **#18-832** ☐ In Stock

-

1

+

C\$44.80

ADD TO CART

Qty 1-10
C\$44.80

Qty 11+
C\$39.20

Volume Pricing
Request Quote

Diameter (mm): 12.50
Cut-On Wavelength (nm): 380.00 ±5
Density (g/cm³): 2.96

Glass/Filter Number: Hoya L38
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Clear
Surface Quality: 60-40
Transformation Temperature (°C): 480
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: UV
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.91
Bevel: Protective as needed
Δλ (nm): <35
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View