

Hoya Y44 (440nm), 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock **#18-855** ☐ In Stock

-

1

+

C\$44.80

ADD TO CART

Qty 1-10
C\$44.80
Qty 11+
C\$39.20
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
12.50

Cut-On Wavelength (nm):
440.00 ±5

Density (g/cm³):
2.59

Glass/Filter Number: Hoya Y44
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Yellow
Surface Quality: 60-40
Transformation Temperature (°C): 570
Thickness (mm): 1.00
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <25
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View