

Hoya Y52 (520nm), 50mm Dia., 2.5mm Thick, Colored Glass Longpass Filter

See More by [Hoya](#)



Stock **#18-876** ☐ In Stock

-

1

+

C\$123.20

ADD TO CART

Qty 1-10

C\$123.20

Qty 11+

C\$109.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00

Cut-On Wavelength (nm):
520.00 ±5

Density (g/cm³):
2.68

Glass/Filter Number: Hoya Y52
Substrate: ☐ Colored Glass
Coating: Uncoated
Color: Yellow
Surface Quality: 60-40
Transformation Temperature (°C): 560
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed
Δλ (nm): <25
TH (%): >85

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View