

IDS Imaging U3-3041LE-C-HQ 1/3" Monochrome Board Level USB 3.1 AutoFocus Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE USB 3.1 AF Autofocus Liquid Lens Board Level Cameras (M12 S-Mount)



Stock **#24-088** ☐ In Stock

[Similar Cameras](#)



1



C\$777.00

ADD TO CART

Qty 1+

C\$777.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Video Output:
USB 3.0

Type:
Monochrome Camera

Manufacturer:
IDS Imaging

Mounting Threads: No Mounting Threads/Tripod Adapter
Image Buffer: Not Specified
Camera Family: uEye LE
Model Number: U3-3041LE-M-GL-AF Rev.1.2
Imaging Sensor: Sony IMX273
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/3"
Resolution (MegaPixels): 1.50
Pixels (H x V): 1,456 x 1,088
Pixel Size, H x V (µm): 3.45 x 3.45
Sensing Area, H x V (mm): 5.03 x 3.75
Frame Rate (fps): 230.00
Pixel Depth: 12 bit
Exposure Time: 40µs - 2s
Connector: USB Type-C
Power Supply: Power over USB
Power Consumption (W): 1 - 2
GPIOs: 2 Flash Output, 2 Trigger Input, 2 GPIO, 2 TWI, 1 Voltage Output, 1 Ground
Synchronization: Hardware Trigger (GPIO); Software Trigger
Dimensions (mm): 36 x 36 x 20 (excludes connectors and lens mount)
Weight (g): 16
Mount: M12 x 0.5 (S-Mbunt)
Housing: Board Level
Interface Port Orientation: Back Back (Right Angle)
Dynamic Range (dB): Not Specified
Operating Temperature (°C): 0 to +55
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 10-pin Wuerth
Machine Vision Standard: USB3 Vision v1.1

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View