

[See all 104 Products in Family](#)

## IDS IMAGING U3-3046LE-C-HQ, 1/3" USB 3 Color Camera Rev. 1.2

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Cameras



Stock #73-670 **1 In Stock**

⊖ 1 ⊕ C\$756<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1+     | C\$756.00 each                |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

|       |           |
|-------|-----------|
| Color | Spectrum: |
|-------|-----------|

### General

|                |               |
|----------------|---------------|
| Color Camera   | Type:         |
| U3-3046LE-C-HQ | Model Number: |
|                | Manufacturer: |

uEye+ LE **Camera Series:**

## Physical & Mechanical Properties

**Dimensions (mm):**  
47 x 46 x 25 (excludes connectors and lens mount)

**Weight (g):**  
38

**Housing:**  
Full

## Sensor

**Image Buffer:**  
Not Specified

**Sensor Format:**  
1/2.9"

**Resolution (Megapixels):**  
1.57

**Frame Rate (fps):**  
230.00

**Pixels (H x V):**  
1,448 x 1,086

**Pixel Size, H x V (µm):**  
3.45 x 3.45

**Sensing Area, H x V (mm):**  
4.995 x 3.746

**Imaging Sensor:**  
Sony IMX273

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Global

**Pixel Depth:**  
12 bit

**Exposure Time:**  
0.025ms - 2000ms

**Dynamic Range (dB):**  
70.00

**Machine Vision Standard:**  
USB3 Vision

## Electrical

**Power Consumption (W):**  
1 - 2

## Hardware & Interface Connectivity

**Interface:**  
USB 3.0

**Connector:**  
USB Type-C

**Power Supply:**  
Power over USB

**GPIOs:**  
N/A

**Synchronization:**  
Hardware Trigger (GPIO); Software Trigger

**Interface Port Orientation:**  
Back Panel (Right Angle)

**GPIO Connector Type:**  
No GPIO Connector Available

## Threading & Mounting

**Mount:**  
S-Mount (M12 x 0.5)

**Mounting Threads:**  
1/4-20 with Tripod Mount Adapter [#16-017](#)

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +55

**Storage Temperature (°C):**  
-20 to +80

## Regulatory Compliance

## Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.

## Calibration Services

---