

[See all 104 Products in Family](#)

## IDS U3-3130CP-C-HQ, USB 3.0, 1/3.6" Color Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Camera, CP Model (Front)

Stock **#24-077** [CONTACT US](#)

C\$868.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$868.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

Color **Spectrum:**

### General

Color Camera **Type:**

U3-3130CP-C-HQ **Model Number:**

IDS Imaging Development Systems **Manufacturer:**

**Camera Series:**

## Physical & Mechanical Properties

**Dimensions (mm):**  
29 x 29 x 29 (excludes connectors and lens mount)

**Weight (g):**  
52

**Housing:**  
Full

## Sensor

**Image Buffer:**  
128MB

**Sensor Format:**  
1/3.6"

**Resolution (Megapixels):**  
0.50

**Frame Rate (fps):**  
396.00

**Pixels (H x V):**  
800 x 600

**Pixel Size, H x V (µm):**  
4.80 x 4.80

**Sensing Area, H x V (mm):**  
3.84 x 2.88

**Imaging Sensor:**  
ON Semi PYTHON 500

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Global

**Pixel Depth:**  
10 bit

**Exposure Time:**  
0.035ms - 303ms

**Dynamic Range (dB):**  
60.00

**Machine Vision Standard:**  
USB3 Vision

## Electrical

**Power Consumption (W):**  
1.7 - 3.9

## Hardware & Interface Connectivity

**Interface:**  
USB 3.0

**Connector:**  
USB 3.0 micro-B, screwable

**Power Supply:**  
Power over USB

**GPIOs:**  
2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Output Supply Voltage, 1 Ground

**Synchronization:**  
Hardware Trigger (GPIO)

**Interface Port Orientation:**  
Back Panel

**GPIO Connector Type:**  
8-pin Hirose connector (HR25-7TR-8PA(73))

## Threading & Mounting

**Mount:**  
C-Mount

**Mounting Threads:**  
¼-20 with Tripod Mount Adapter [#16-017](#)

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +55

**Storage Temperature (°C):**  
-20 to +60

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

---

[Contains SVHC\(s\)](#) **REACH 241:**

---

## Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.

## Calibration Services

---

;