

[See all 65 Products in Family](#)

IDS Imaging U3-3884LE-C-HQ-VU 1/1.8" Color USB3 Camera Rev. 1.2

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye LE/XLE Camera (C/CS - Mount, Full Housing, Front View)



Stock #78-149 [CONTACT US](#)

- 1 + C\$635⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$635.60 each
Need More?	Request Quote

Product Downloads

Color Spectrum:

General

Color Camera Type:

Sensor

1/1.8" Sensor Format:

6.40	Resolution (Megapixels):
54.00	Frame Rate (fps):
3,088 x 2,076	Pixels (H x V):
2.40 x 2.40	Pixel Size, H x V (µm):
Sony IMX178	Imaging Sensor:
Rolling	Shutter Type:
Hardware & Interface Connectivity	
Vertical	Connector:
Threading & Mounting	
C-Mount	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Up to 8.0MP Resolution with Framerates up to 230fps
- Board Level Options with C/CS-Mount or S-Mount Available
- GenICam USB3 Vision Compliant

IDS Imaging uEye LE/XLE USB3.1 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GenICam and USB3 Vision standards for ease of software development and integration. These cameras are available in board-level or housed options with S-Mount or C/CS-Mount versions. The C/CS-Mount configurations come with a 5mm spacer to easily adapt between C-Mount and CS-Mount lenses. IDS Imaging uEye LE/XLE USB3.1 Cameras are ideal for small device construction, medical technology, robotics, and machine vision applications. With a compact design, the XLE version is suitable for integration into embedded systems whereas the LE version is suitable for small device projects.

Calibration Services

;