

[See all 105 Products in Family](#)

## IDS U3-3890SE-M-GL, USB 3.0, 1/1.7" Monochrome Camera

See More by [IDS Imaging Development Systems](#)



IDS Imaging uEye+ USB3 Camera, SE Model (Front)



Stock #24-139 **4 In Stock**

- 1 + C\$1,071<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	C\$1,071.00 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

Monochrome **Spectrum:**

### General

Monochrome Camera **Type:**

U3-3890SE-M-GL **Model Number:**

**Manufacturer:**

uEye+ SE **Camera Series:**

## Physical & Mechanical Properties

**Dimensions (mm):**  
34 x 44 x 47 (excludes connectors and lens mount)

**Weight (g):**  
110

**Housing:**  
Full

## Sensor

**Image Buffer:**  
128MB

**Sensor Format:**  
1/1.7"

**Resolution (Megapixels):**  
12.00

**Frame Rate (fps):**  
33.00

**Pixels (H x V):**  
4,000 x 3,000

**Pixel Size, H x V (µm):**  
1.85 x 1.85

**Sensing Area, H x V (mm):**  
7.4 x 5.55

**Imaging Sensor:**  
Sony IMX226

**Type of Sensor:**  
Progressive Scan CMOS

**Shutter Type:**  
Rolling

**Pixel Depth:**  
12 bit

**Exposure Time:**  
0.13ms - 609ms

**Dynamic Range (dB):**  
68.00

**Machine Vision Standard:**  
USB3 Vision

## Electrical

**Power Consumption (W):**  
2 - 3.6

## Hardware & Interface Connectivity

**Interface:**  
USB 3.0

**Connector:**  
USB Type-C, screwable

**Power Supply:**  
Power over USB

**GPIOs:**  
2 Flash Output, 2 Trigger Input, 2 GPIO, 1 Voltage Output, 1 Ground

**Synchronization:**  
Hardware Trigger (GPIO); Software Trigger

**Interface Port Orientation:**  
Back Panel

**GPIO Connector Type:**  
8-pin Hirose connector (HR25-7TR-8PA(73))

## Threading & Mounting

**Mount:**  
C-Mount

**Mounting Threads:**  
¼-20 with Tripod Mount Adapter [#16-017](#)

## Environmental & Durability Factors

**Operating Temperature (°C):**  
0 to +55

**Storage Temperature (°C):**  
-20 to +60

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

---

[Contains SVHC\(s\)](#) **REACH 241:**

---

## Product Details

- Standard (SE), Compact (CP), and Ultra Compact (XCP) Housing Options Available
- C-Mount with Large Format CMOS Sensors up to 1.1"
- Up to 20.44MP Resolution with Framerrates up to 396fps

IDS Imaging uEye CP/XCP/SE USB3 Cameras utilize [IDS Imaging's peak SDK platform](#) that supports GeniCam and USB3 Vision standards for easy software development and integration. The CP cameras are the industry standard size of 29 x 29 x 29mm and work for almost any application. The XCP cameras have an ultra-compact size of 29 x 29 x 17mm and are an excellent option for price-sensitive, single-camera applications. The SE cameras have a larger housing size of 34 x 44 x 47mm to allow for exceptional heat management and are ideal for noise and heat-sensitive applications. IDS Imaging uEye CP/XCP/SE USB3 Cameras are ideal for manufacturing, industrial, and automation applications.

## Calibration Services

---