

InfiniProbe S-80 Video Microscope (0-8.0X)

See More by [Infinity Photo-Optical Company](#)



Stock **#58-809** **1 In Stock**

-

1

+

C\$4,802⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$4,802.00 each
Need More?	Request Quote

Product Downloads

General

Long Distance Microscope

Type:

Physical & Mechanical Properties

209.79

Weight (g):

Optical Properties

1.1mm

Horizontal Field of View, 2/3" Sensor:

0.8mm	Horizontal Field of View, 1/2" Sensor:
0X - 8.0X	Primary Magnification PMAG:
18 - ∞	Working Distance (mm):
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
C-Mount	Mount:
Regulatory Compliance	
Compliant	RoHS 2015:
Compliant	Reach 224:
View	Certificate of Conformance:

Product Details

- Available in Standard and Right Angle Versions
- Focuses From Infinity to 32, 28, and 18mm Respectively
- Max. Sensor Format 2/3"
- Magnification From 2.5X to 8.0X
- Direct Video C-Mbunt Coupling

The InfiniProbe™ Video Microscope series provides the advantages of a continuously focusable microscope in a compact design. Using the Dynamic Focusing System (DFS), the InfiniProbe™ is capable of focusing from infinity down to its specified minimum working distance. Detail and resolution grow as the magnification continuously increases. Entire objects can be hand-held and rotated while, at the same time, remaining completely in focus. Then, a specific detail may be zeroed in at truly microscopic magnifications. To increase the versatility of the InfiniProbe™ series, three models with magnifications of 2.5X, 3.2X, and 8X are offered. All magnification ranges are also offered in Right Angle versions. In addition to the three available magnification ranges, Infinity has created a 2X doubler tube ([#39-686](#)) that when combined with the InfiniProbe™, will increase the magnification to twice it's stated value. InfiniProbe™ can be used with all C-mount and CS-mount video cameras.

Technical Information

