

IR M49 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock #21-442 ☐ In Stock

-

1

+

C\$240.80

ADD TO CART

Qty 1-9

C\$240.80

Qty 10+

C\$229.88

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):
200-772

Clear Aperture CA (mm):
44.00

Coating:
Hard Coated

Filter Thread:

M49 x 0.75
Color: IR
Center Wavelength CWL (nm): 850.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 160.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 51.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View