

IR M58 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock **#21-731** [CONTACT US](#)



1



C\$273.00

ADD TO CART

Qty 1-9

C\$273.00

Qty 10+

C\$259.42

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):
200-789

Clear Aperture CA (mm):
53.00

Coating:
Hard Coated

Filter Thread:

M58 x 0.75
Color: IR
Center Wavelength CWL (nm): 850.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 160.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 60.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View