

ISO-14524 Reflective Camera Contrast Chart



Stock **#58-944** 2 In Stock

-

1

+

C\$676^{.20}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$676.20 each
Qty 5+	C\$644.00 each
Need More?	Request Quote

Product Downloads

General

NIST Certification:

No

Physical & Mechanical Properties

Length (mm):

395.00

Pattern Size (mm):

200 x 356

Width (mm):

240.00

12	Number of Patches:
31.4 x 31.4	Patch Size (mm):
Optical Properties	
Reflective Photo Paper	Substrate:
Background: 0.84 Individual Patches: 0.1, 0.2, 0.31, 0.43, 0.56, 0.70, 0.87, 1.05, 1.27, 1.53, 1.86, 2.30	Optical Density OD (Average):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Determines Dynamic Range of Cameras
 - 12 gray level patches
- The Reflective Contrast Target is designed to determine the range of optical density that an imaging system can capture. This target complies with ISO-14524 specifications.