

Isuzu ISK157, 50 Dia., Heat Absorbing Colored Glass Filter



Isuzu ISK Colored Glass Heat Absorbing Filters

Stock **#15-712** ☐ In Stock

-

1

+

C\$114.80

ADD TO CART

Qty 1-9

C\$114.80

Qty 10+

C\$100.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00 ±0.25

Optical Density OD (Average):
3.84 @ 1064nm

Clear Aperture CA (mm):
45

Cut-Off Wavelength (nm): 698.00 ±13
Density (g/cm³): 2.6
Glass/Filter Number: Isuzu ISK157
Substrate: ☐ Heat Absorbing Glass
Minimum Transmission (%): ≥80 @ 400 - 550nm
Operatiny Temperature (°C): 300 Maximum
Coating: Uncoated
Index of Refraction n_d: 1.518
Surface Quality: 60-40
Transformation Temperature (°C): 566
Thickness (mm): 3.00 ±0.38
Type: IR Cut-Off Filter
Parallelism (arcmin): 3
Reflection Factor P_d: 0.92
Wavelength Range (nm): 300 - 2700
Surface Flatness (P-V): 3λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View