

JAI 2m Power and GPIO Cable, 6-pin Hirose and Flying Leads



Stock #29-176 **CLEARANCE** 1 In Stock

- 1 + C\$140.⁹³

ADD TO CART

Volume Pricing

Qty 1+ C\$140.93 each

Need More? [Request Quote](#)

Product Downloads

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- Up to 12.3 MP Resolution
- USB and GigE Versions Available
- Longest Industry Warranty (6 Years)

JAI® Go-X Series Cameras are designed to be compact, industrial grade, reliable cameras with excellent image quality. Featuring industrial grade shock and vibration ratings (80G/10G) as well as excellent thermal dissipation, these cameras are ideal for factory floors and assembly lines. Designed with a variety of capabilities, these cameras are capable of region-of-interest (ROI), blemish compensation with shading correction, and 8, 10, and 12-bit

output. JAI® Go-X Series Cameras are available in resolutions ranging from 2.3 to 12.3MP with both USB or Gigabit Ethernet (GigE) outputs. Downloadable software is [available](#) for both GigE and USB options.

;