

[See all 3 Products in Family](#)

108.0mm Max Optic Dia., Jaw Clamp and 6" Kinematic Mount



#53-040

Stock **#53-040** 2 In Stock

-

1

+

C\$1,708⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-4	C\$1,708.00 each
Qty 5-9	C\$1,589.98 each
Qty 10-25	C\$1,511.16 each
Need More?	Request Quote

Product Downloads

General	
Adjustable - Tip-Tilt	Type:
Circular	Type of Optics:

Physical & Mechanical Properties

4.25	Clear Aperture CA (inches):
------	-----------------------------

3.35	Weight (lbs):
Black Anodized Aluminum	Construction:
±4.0	Fine Tilt Angle (°):
Threading & Mounting	
5.50 - 108.00	Size of Compatible Optics (mm):
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Stand Alone Jaw Clamp Mounts (8-32 Mounting) or with Kinematic Frame
 - Accepts up to 4-¼" Diameters
 - Fine Angular Resolution Kinematic
- An affordable self-centering jaw clamp for use with components up to 4-¼" Dia. Mounted alone on the 8-32 tapped hole in the base, or to the 6" kinematic frame, the jaw clamp precisely centers your components without the danger of warping them with clumsy edge clips. The kinematic mount has an angled base, to allow fastening by either ¼-20 cap screws or un-fastened for stand-alone use. Locking screw allows jaw position to be fixed to secure against accidental movement. Mount features precise kinematic pivot movement (two-axis tilt) with orthogonal three-point suspension. Adjustment is made by three 64 pitch screws. Construction is black anodized aluminum.

Technical Information

