

[See all 7 Products in Family](#)

Leica N Plan 40x Objective

See More by [Leica](#)



Leica Achromatic N Plan Objectives

Stock **#29-534** **5 In Stock**

C\$3,108⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$3,108.00 each
Need More?	Request Quote

Product Downloads

General

Compatible Tube Lens Focal Length (mm):
Focal Length: 200mm

Style:
Infinity Corrected

Manufacturer:
Leica

Optical Properties

Compatible Cover Glass Thickness (mm):
0.17

5.00	Focal Length FL (mm):
40X	Magnification:
0.75	Numerical Aperture NA:
0.36	Resolving Power (μm):
0.32	Depth of Field (μm):
0.37	Working Distance (mm):
22	Field Number (mm):
45.0	Parfocal Length (mm):
Dry	Immersion Liquid:

Threading & Mounting

M25 x 0.75	Mounting Threads:
------------	--------------------------

Regulatory Compliance

View	Certificate of Conformance:
----------------------	------------------------------------

Product Details

- Excellent Color Correction and Flatness of Field
- 5X to 100X Magnifications Available
- Designed for Transmitted Light and DIC Illumination Techniques
- M25 x 0.75 Threading
- Low-Cost Alternative, [Hi Plan](#) Objectives Available

Leica Achromatic N Plan Objectives are powerful objectives with improved color performance over the visible spectral range and offer excellent field flatness up to a 25mm field of view. These objectives are available in magnifications from 5X, 10X, 20X, 40X, 50X, and 100X. Leica Achromatic N Plan Objectives are designed for varying illumination techniques such as transmitted light and differential interference contrast (DIC). These objectives are ideal for life science and materials research, industrial quality control and failure analysis, and medical and surgical imaging applications.