

Light Red M43 x 0.75 Mounted Machine Vision Filter



Mounted Machine Vision Filters

Stock **#21-695** ☐ In Stock



1



C\$214.20

ADD TO CART

Qty 1-9

C\$214.20

Qty 10+

C\$203.98

Volume Pricing

[Request Quote](#)

Get Product Downloads

Blocking Wavelength Range (nm):

200-570, 700-1117

Clear Aperture CA (mm):

38.00

Coating:

Hard Coated

Filter Thread:

M43 x 0.75
Color: Light Red
Center Wavelength CWL (nm): 635.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 60.00
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0
Outer Diameter (mm): 45.00
Substrate Thickness (mm): 1.3
Type: Mounted Imaging Filter
Minimum Transmission (%): ≥85

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View