

# Lumenera INFINITY 3-6UR Microscopy Monochrome Camera

See More by [Teledyne DALSA](#)



Stock **#33-288** ☐ In Stock

-

1

+

C\$8,400.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1+                        |
| C\$8,400.00                   |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads

**Video Output:**  
USB 3.0

**Type:**  
Monochrome Microscopy Camera

**Manufacturer:**  
Teledyne Lumenera

**Mounting Threads:**  
2 x 1/4-20 (Integrated into Housing)

|                                                                     |
|---------------------------------------------------------------------|
| <b>Image Buffer:</b><br>Not Specified                               |
| <b>Camera Family:</b><br>INFINITY                                   |
| <b>Model Number:</b><br>INFINITY3-6UR                               |
| <b>Imaging Sensor:</b><br>Sony ICX694                               |
| <b>Type of Sensor:</b><br>Progressive Scan CCD                      |
| <b>Type of Shutter:</b><br>Global                                   |
| <b>Camera Sensor Format:</b><br>1"                                  |
| <b>Resolution (MegaPixels):</b><br>6.00                             |
| <b>Pixels (H x V):</b><br>2,752 x 2,192                             |
| <b>Pixel Size, H x V (µm):</b><br>4.54 x 4.54                       |
| <b>Sensing Area, H x V (mm):</b><br>12.49 x 9.95                    |
| <b>Frame Rate (fps):</b><br>27.00                                   |
| <b>Pixel Depth:</b><br>8/14 bit                                     |
| <b>Exposure Time:</b><br>23µs - 1.79s (video)                       |
| <b>Power Supply:</b><br>Power over USB                              |
| <b>Power Consumption (W):</b><br>6                                  |
| <b>GPIOs:</b><br>N/A                                                |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO)                  |
| <b>Dimensions (mm):</b><br>97.8 x 69.8 x 50.8 (excludes lens mount) |
| <b>Weight (g):</b><br>395                                           |
| <b>Mount:</b><br>C-Mount                                            |
| <b>Housing:</b><br>Full                                             |
| <b>Interface Port Orientation:</b><br>Side Panel                    |
| <b>Dynamic Range (dB):</b><br>64.8                                  |
| <b>Operating Temperature (°C):</b><br>0 to +50                      |
| <b>Storage Temperature (°C):</b><br>-30 to +70                      |
| <b>GPIO Connector Type:</b><br>8-pin Hirose (MRX)                   |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br>Compliant                                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |