

M30.5 x 0.5 Mounted UV/IR Cut-Off Filter



Stock **#49-809** [CONTACT US](#)

- 1 + **C\$270.20**

ADD TO CART

Qty 1-9
C\$270.20
Qty 10+
C\$248.50
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
28.0

Filter Thread:
M30.5 x 0.50

Cut-Off Wavelength (nm):
690.00

Cut-On Wavelength (nm):
390.00

Index of Refraction n_d: 1.52 Substrate, Varies by Layer
Note: AR Coating: Both Surfaces Multi-Layer
Outer Diameter (mm): 32.0
Substrate: ☐ Float Glass
Substrate Thickness (mm): 2.0
Surface Quality: 60-40
Thickness with Mount (mm): 6.4
Type: Mounted Imaging Filter

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant